
Quick-Lock Connectors

If it has to be quick!




Advantages

- Drip protection, thanks to integrated locking valve
- Closed system, for drip-free separation
- Very little air ingress
- Minimal contamination
- No outwashing of air bubbles from the system is necessary
- Intuitive connection
- User-friendly, ergonomic design enables a safe and reliable connection
- Chemically resistant materials
- Secure connection and reliable performance for many applications



Specifications

Pressure	Vacuum 15 psi @ 1.0 bar		
Temperature	0°C to 49°C (32°F to 120°F)		
Materials	Main Components: Glass-filled Polypropylene, PEEK, Polypropylene Lock: PEEK® Springs: Stainless Steel 316 O-Rings: EPDM		
Colour	Grey		
Capillary Size:	3.2 mm OD (1/8") 2.3 mm OD 1.6 mm OD (1/16")		
Discharge	0.02 cc per disconnection @ 15 psi		
Uptake	0.01 cc per connection		















Ordering Information

Fig.	Part No.	Description	PU
A	360 189	Quick-Lock Connector Set I for capillaries Contains 360 190 (■) and 360 179 (■)	1 pc.
B	360 190	Quick-Lock Connector (m)	1 pc.
G	360 179	Quick-Lock Connector (f)	1 pc.
D	360 183	Quick-Lock Connector Set II for Safety Caps With adapter for screwing into the standard connectors of Safety Caps (UNF 1/4" 28G)	1 pc.
8	360 180	Quick-Lock Connector (m) for screwing into the standard connectors of Safety Caps (UNF 1/4" 28G)	1 pc.







S.C.A.T. Europe GmbH

Waldecker Straße 7 64546 Mörfelden-Walldorf Germany



+49 (0) 61 05 / 30 55 86 - 0



info@scat-europe.com



www.scat-europe.com